



### 选件



### 型号

型号	额定功率 W	额定转矩 Ncm	额定电流 A	峰值电流 A	标称电压 V	额定转速 rpm	转矩常数 Ncm/A	转子的转动惯量 gcm <sup>2</sup>	机身长度 "A" mm	重量 kg
DB28S01	4.2	0.5	0.45	1.3	15	8000	1.43	2.35	28	0.06
DB28M01	14.6	1.4	0.95	2.7	24	10000	1.69	3.69	38	0.082
DB28L01	20.9	5	1.45	4.5	24	4000	3.56	10.98	77	0.195

### 尺寸图 (单位MM)

