



选件



型号

型号	额定功率 W	额定转矩 Ncm	额定电流 A	峰值电流 A	标称电压 V	额定转速 rpm	转矩常数 Ncm/A	转子的转动惯量 gcm ²	机身长度 "A" mm	重量 kg
DB56L036030-A	94	30	4	12	36	3000	7.3	260	76	1
DB56C036030-A	141	45	5.4	16.2	36	3000	8	360	96	1.1
DB56D036030-A	188	60	7.5	22.5	36	3000	8	460	116	1.2

尺寸图 (单位MM)

