



### 选件



### 型号

型号	额定功率 W	额定转矩 Ncm	额定电流 A	峰值电流 A	标称电压 V	额定转速 rpm	转矩常数 Ncm/A	转子的转动惯量 gcm <sup>2</sup>	机身长度 "A" mm	重量 kg
DB80S048030	283	90	6.9	20	48	3000	13	544	87	1.5
DB80M048030	534	170	14	40	48	3000	12	1020	108	2.1
DB80L048030	706	225	18.75	65	48	3000	12	1360	123	2.6
DB80C048030	942	300	25	85	48	3000	12	1900	143	3.3

### 订货代码



**DB80S048030-**  
**A = 不带编码器**  
**ENM05J = 带增量式编码器**

### 尺寸图 (单位MM)

