



### 选件



### 型号

型号	额定功率 W	额定转矩 Ncm	额定电流 A	峰值电流 A	标称电压 V	额定转速 rpm	转矩常数 Ncm/A	转子的转动惯量 gcm <sup>2</sup>	机身长度 "A" mm	重量 kg
DF45S024050	30	5	1.58	4.8	24	5000	3.55	99	18	0.08
DF45M024053	50	8.4	2.36	7	24	5260	3.35	135	21.6	0.12
DF45L024048	65	13	3.26	9.5	24	4840	3.69	181	27	0.15

### 订货代码




### 配件



**DF45S024050-**  
A = PCB 接头  
A2 = 带接头的电缆

**ZK-JST-PHR-6-0.3M** 霍尔电缆  
DF45 0.3米  
**ZK-JST-VHR-5N-0.3M** 电机电缆  
DF45 0.3米

### 尺寸图 (单位MM)



### 尺寸图 (单位MM)

DF45-A2

