



选件



型号

型号	额定功率 W	额定转矩 Ncm	额定电流 A	峰值电流 A	标称电压 V	额定转速 rpm	转矩常数 Ncm/A	转子的转动惯量 gcm ²	机身长度 "A" mm	重量 kg
DS16S012220-A	3.7	0.16	0.4	1.18	12	22000	0.406	4	28	0.03
DS16M024250-A	10	0.4	0.5	1.6	24	25000	0.75	6.6	40	0.04
DS16L024240-A	25	1	1.33	4	24	24000	0.748	10.2	56	0.065

尺寸图 (单位MM)

