

### 选件



### 型号

型号	额定功率 W	额定转矩 Ncm	额定电流 A	峰值电流 A	标称电压 V	额定转速 rpm	转矩常数 Ncm/A	转子的转动惯量 gcm <sup>2</sup>	机身长度 "A" mm	重量 kg
DS28M024080	15.1	1.8	0.86	2.6	24	8000	2.1	8.8	45	0.14
DS28L024080	29	3.5	1.35	4	24	8000	2.6	16	67	0.22

### 尺寸图 (单位MM)

