



选件



型号

型号	推力 N	速度 mm/s	相电流 A	分辨率 $\mu\text{m}/\text{步}$	相电阻 Ohm	相电感 mH	丝杆直径 mm	导程 mm	机身长度 "A" mm	丝杆长度 "L" mm	重量 kg
LSA281S10-A-UGAQ-152	210	19	1	3.175	2.7	2.5	4.76	0.635	33	152	0.13
LSA281S10-B-UGAQ-152	210	19	1	3.175	2.7	2.5	4.76	0.635	33	152	0.13
LSA281S10-A-UGFC-152	50	120	1	25.4	2.7	2.5	4.76	5.08	33	152	0.13
LSA281S10-B-UGFC-152	50	120	1	25.4	2.7	2.5	4.76	5.08	33	152	0.13
LSA281S10-A-THCA-152	93.4	35	1	10	2.7	2.5	5	2	33	152	0.13
LSA281S10-B-THCA-152	93.4	35	1	10	2.7	2.5	5	2	33	152	0.13

订货代码

LSA281S10-
A... = 单轴端
B... = 双轴端



配件

LSNUT-AAAA-UGAQ 螺纹螺母 - POM
LSNUT-AAAA-UGFC 螺纹螺母 - POM
LSNUT-AAAA-THCA 螺纹螺母 - POM
NANOLUBE-50G 润滑剂




警告


数据表中指定的力和额定功率基于 10% 至 20% 的占比，必须将其相应降低才能获得更大的值。应避免运行至固定的限位挡块。







尺寸图 (单位MM)



尺寸图 (单位MM)



速度推力曲线



速度推力曲线

