



选件



型号

型号	推力 N	速度 mm/s	相电流 A	分辨率 μm/步	相电阻 Ohm	相电感 mH	丝杆直径 mm	导程 mm	丝杆长度 "L" mm	机身长度 "A" mm	重量 kg
LSA421S14-A-UKGI-152	152	80	1.4	31.75	2	2.8	6.35	6.35	152	33.4	0.26
LSA421S14-B-UKGI-152	152	80	1.4	31.75	2	2.8	6.35	6.35	152	33.4	0.26
LSA421L18-B-TJCA-152	369	50	1.8	10	1.75	3.25	6	2	152	47.4	0.4
LSA421L18-B-UKGI-152	275	80	1.8	31.75	1.75	3.4	6.35	6.35	152	47.4	0.4

订货代码

LSA421S14-
A ... = 单轴端
B ... = 双轴端



配件

LSNUT-AAAE-TJCA 螺纹螺母 - POM
LSNUT-AAAE-UKGI 螺纹螺母 - POM
LSNUT-AEAE-TJCA 预装螺纹螺母 - POM
LSNUT-AEAE-UKGI 预装螺纹螺母 - POM
ZK-JST-EHR-6-0.5M-S 电机线缆 0.5米
NANOLUBE-50G 润滑剂




警告


数据表中指定的力和额定功率基于 10% 至 20% 的占空比，必须将其相应降低才能获得更大的值。应避免运行至固定的限位挡块。



尺寸图 (单位MM)



尺寸图 (单位MM)



速度推力曲线

