



### 选件



### 型号

型号	相电流 A	保持转矩 Ncm	相电阻 Ohm	相电感 mH	转子的转动惯量 gcm <sup>2</sup>	重量 kg	机身长度 "A" mm
SC3518S1204	1.2	10	1.7	1.5	11	0.15	30
SC3518M1204	1.2	18	2.5	2.9	20	0.18	39.5
SC3518L1204	1.2	32	3.8	5.2	43	0.3	56.5

### 订货代码


**SC3518S1204-**  
A = 单轴端  
B = 双轴端



### 配件

**ZK-JST-EHR-6-0.5M-S** 电机线缆 0.5米  
**ZD-D28** 减震器  
**ZD-D40** 减震器

### 尺寸图 (单位MM)



### 力矩曲线

