



选件




型号

型号	相电流 A	保持转矩 Ncm	相电阻 Ohm	相电感 mH	转子的转动惯量 gcm <sup>2</sup>	重量 kg	机身长度 "A" mm
SCA2018S0604	0.6	2.2	6.5	2.6	2	0.06	33
SCA2018M0804	0.8	3.6	5.6	2.3	2.9	0.07	40

订货代码

**SCA2018S0604-**  
A = 单轴端  
B = 双轴端

尺寸图 (单位MM)



力矩曲线

