



选件



型号

型号	相电流 A	保持转矩 Ncm	相电阻 Ohm	相电感 mH	转子的转动惯量 gcm ²	重量 kg	机身长度 "A" mm
ST2018S0604	0.6	1.8	6.5	1.7	2	0.06	33
ST2018M0804	0.8	3	5.4	1.5	3.6	0.08	42
ST2018L0804	0.8	3.6	6	2.2	4.3	0.09	48


订货代码

ST2018S0604-
A = 单轴端
B = 双轴端

配件

ZK-JST-VL-4 适用于 XHP4 插头的延长线

尺寸图 (单位MM)



力矩曲线

