



选件



型号

型号	相电流 A	保持转矩 Ncm	相电阻 Ohm	相电感 mH	转子的转动惯量 gcm ²	重量 kg	机身长度 "A" mm
ST2818S1006	0.67	6.08	2.8	1	9	0.11	31.5
ST2818M1006	0.67	10.61	3.4	1.2	12	0.176	44.5
ST2818L1006	0.67	12.73	4.6	1.8	18	0.25	50.5
ST2818L1404	1.4	11.7	2.3	1.8	18	0.25	50.5

*电流和保持力矩是用双极性串联接法测得。电阻和电感值是用单极性接法测得。


订货代码

ST2818S1006-
A = 单轴端
B = 双轴端

配件

ZK-JST-VL-4 适用于 XHP4 插头的延长线
ZK-JST-VL-6 适用于 XHP6 插头的延长线
ZD-D28 减震器

尺寸图 (单位MM)



力矩曲线

