



选件



型号

型号	相电流 A	保持转矩 Ncm	相电阻 Ohm	相电感 mH	转子的转动惯量 gcm ²	重量 kg	机身长度 "A" mm
ST4118X0404	0.4	17	24	36	20	0.15	26
ST4118X1404	1.4	9	2	1.6	20	0.15	26
ST4118S0206	0.16	21.21	75	53	38	0.2	30.5
ST4118S0406	0.25	22.63	30	21.7	38	0.2	30.5
ST4118S0706	0.49	22.63	7.6	6.8	38	0.2	30.5
ST4118S1006	0.67	21.21	3.9	2.8	38	0.2	30.5
ST4118S1404	1.4	20	2	3	38	0.2	30.5
ST4118M0406	0.28	39.6	30	25	57	0.24	38
ST4118M0706	0.49	39.6	9.5	8	57	0.24	38
ST4118M0906	0.64	39.6	5.7	5	57	0.24	38
ST4118M1206	0.85	39.6	3.1	2.9	57	0.24	38
ST4118M1404	1.4	24	1.2	1.7	57	0.24	38
ST4118M1804	1.8	28	1.1	1.85	57	0.24	38
ST4118L0804	0.8	50	9.3	17	83	0.34	48.5
ST4118L1206	0.85	49.5	3.3	3.4	82	0.34	48.5
ST4118L1804	1.8	50	1.75	3.3	82	0.34	48.5
ST4118L3004	3	50	0.63	1.03	82	0.34	48.5
ST4118D1804	1.8	80	3	7	102	0.5	60
ST4118D3004	3	80	1.1	2.7	102	0.5	60

*电流和保持力矩是用双极性串联接法测得。电阻和电感值是用单极性接法测得。


订货代码

ST4118X0404-
A = 单轴端
B = 双轴端



配件

ZK-JST-VL-4
适用于 XHP4 插头的延长线
ZK-JST-VL-6
适用于 XHP6 插头的延长线
ZD-D40 减震器
ZD-DF40 减震器







尺寸图 (单位MM)









力矩曲线



力矩曲线



力矩曲线



力矩曲线

