



选件



型号

型号	相电流 A	保持转矩 Ncm	相电阻 Ohm	相电感 mH	转子的转动惯量 gcm ²	重量 kg	机身长度 "A" mm
ST4209X1004	1	17	8.7	18	20	0.15	22
ST4209S0404	0.42	17.6	13	7.5	35	0.22	33.5
ST4209S1006	0.67	21.21	4.2	4	35	0.22	33.5
ST4209S1404	1.33	22	2.1	5.2	35	0.22	33.5
ST4209M1206	0.85	35.36	3.3	4	54	0.28	39.5
ST4209M1704	1.68	36	1.9	4	54	0.28	39.5
ST4209L1206	0.85	43.84	3.3	4.8	68	0.35	47.5
ST4209L1704	1.68	44	1.8	5	68	0.35	47.5

*电流和保持力矩是用双极性串联接法测得。电阻和电感值是用单极性接法测得。

订货代码




配件







ST4209X1004-
A = 单轴端
B = 双轴端

ZK-JST-VL-4
适用于 XHP4 插头的延长线
ZK-JST-VL-6
适用于 XHP6 插头的延长线
ZD-D40 减震器
ZD-DF40 减震器

尺寸图 (单位MM)



力矩曲线



力矩曲线

