



选件



型号

| 型号 | 相电流 A | 保持转矩 Ncm | 相电阻 Ohm | 相电感 mH | 转子的转动惯量 gcm ² | 重量 kg | 机身长度 "A" mm |
|-------------|-------|----------|---------|--------|--------------------------|-------|-------------|
| ST5918X1008 | 0.71 | 53.74 | 5 | 5.4 | 135 | 0.49 | 41 |
| ST5918X2008 | 1.41 | 53.74 | 1.2 | 1.3 | 135 | 0.49 | 41 |
| ST5918X3008 | 2.12 | 53.74 | 0.5 | 0.54 | 135 | 0.49 | 41 |
| ST5918S1008 | 0.71 | 98.99 | 6.2 | 7.5 | 275 | 0.65 | 51 |
| ST5918S2008 | 1.41 | 98.99 | 1.5 | 2.6 | 275 | 0.65 | 51 |
| ST5918S3008 | 2.12 | 98.99 | 0.72 | 0.9 | 275 | 0.65 | 51 |
| ST5918M1008 | 0.71 | 124.45 | 6.9 | 14 | 300 | 0.7 | 56 |
| ST5918M2008 | 1.41 | 124.45 | 1.7 | 2.5 | 300 | 0.7 | 56 |
| ST5918M3008 | 2.12 | 124.45 | 0.7 | 1.3 | 300 | 0.7 | 56 |
| ST5918L1008 | 0.71 | 186.68 | 8.8 | 15.4 | 480 | 1 | 76 |
| ST5918L2008 | 1.41 | 186.68 | 2.4 | 5.1 | 480 | 1 | 76 |
| ST5918L3008 | 2.12 | 186.68 | 1 | 1.9 | 480 | 1 | 76 |
| ST5918L4508 | 3.18 | 186.68 | 0.5 | 0.95 | 480 | 1 | 76 |

*电流和保持力矩是用双极性串联接法测得。电阻和电感值是用单极性接法测得。


订货代码

ST5918X1008-
A = 单轴端
B = 双轴端





配件

ZD-D56 减震器
ZD-DF56 减震器







尺寸图 (单位MM)






力矩曲线



力矩曲线



力矩曲线



混合式步进电动机