



订货代码



螺栓-...-
 200 = 螺栓长度, 带端加工
 300 = 螺栓长度, 带端加工
 1000 = 螺栓长度, 不带端加工

技术参数

丝杆材料	不锈钢 (不耐酸和盐水)
抗拉强度	760 ²
螺距延迟	± 0.1/300 mm/截面

型号

型号	丝杆直径 mm	中心直径 mm	导程 mm	配套电机	标准轴向间隙 mm	最大轴向间隙 mm	材料编号	丝杆长度 mm
SCREW-ABA-UGAQ-200	4.76	3.579	0.635	LA...-UGAQ	0.03	±0.06	1.4301	200
SCREW-ABA-UGAQ-300	4.76	3.579	0.635	LA...-UGAQ	0.03	±0.06	1.4301	300
SCREW-AAA-UGAQ-1000	4.76	3.579	0.635	LA...-UGAQ	0.03	±0.06	1.4301	1000
SCREW-ABA-UGFC-200	4.763	2.868	5.08	LA...-UGFC	0.04	±0.08	1.4301	200
SCREW-ABA-UGFC-300	4.763	2.868	5.08	LA...-UGFC	0.04	±0.08	1.4301	300
SCREW-AAA-UGFC-1000	4.763	2.868	5.08	LA...-UGFC	0.04	±0.08	1.4301	1000
SCREW-ABA-UIAP-200	5.56	4.402	0.6096	LA...-UIAP	0.04	±0.06	1.4301	200
SCREW-ABA-UIAP-300	5.56	4.402	0.61	LA...-UIAP	0.04	±0.06	1.4301	300
SCREW-AAA-UIAP-1000	5.56	4.402	0.6096	LA...-UIAP	0.04	±0.06	1.4301	1000
SCREW-ABA-UKAS-200	6.35	4.983	0.7938	LA...-UKAS	0.04	±0.07	1.4301	200
SCREW-ABA-UKAS-300	6.35	4.983	0.7938	LA...-UKAS	0.04	±0.07	1.4301	300
SCREW-AAA-UKAS-1000	6.35	4.983	0.7938	LA...-UKAS	0.04	±0.07	1.4301	1000
SCREW-ABA-UKBN-200	6.35	4.107	1.5875	LA...-UKBN	0.05	±0.08	1.4301	200
SCREW-ABA-UKBN-300	6.35	4.107	1.5875	LA...-UKBN	0.05	±0.08	1.4301	300
SCREW-AAA-UKBN-1000	6.35	4.107	1.5875	LA...-UKBN	0.05	±0.08	1.4301	1000
SCREW-ABA-UKDE-200	6.35	4.107	3.175	LA...-UKDE	0.05	±0.09	1.4301	200
SCREW-ABA-UKDE-300	6.35	4.107	3.175	LA...-UKDE	0.05	±0.09	1.4301	300
SCREW-AAA-UKDE-1000	6.35	4.107	3.175	LA...-UKDE	0.05	±0.09	1.4301	1000
SCREW-ABA-UKGI-200	6.35	4.107	6.35	LA...-UKGI	0.05	±0.09	1.4301	200
SCREW-ABA-UKGI-300	6.35	4.107	6.35	LA...-UKGI	0.05	±0.09	1.4301	300
SCREW-AAA-UKGI-1000	6.35	4.107	6.35	LA...-UKGI	0.05	±0.09	1.4301	1000

尺寸图 (单位MM)

