



技术参数

安全性	软启动
认证	CE/UL/TÜV
连接类型	丝杆夹
紧固类型	DIN 载运导轨 TS-35/7.5 或 15
保护电路	过载/过压保护、防短路、过温

型号

型号	输入电压 V	输出电压 V	输出电流 A	输出功率 W	输入电流 (冷启动) A	长度 "L" mm	重量 kg
NTS-12V-3.5A	85...264VAC 120...370VDC	12	3.5	42	56 / 230 VAC	93	0.31
NTS-24V-2A	85...264VAC 120...370VDC	24	2	48	56 / 230 VAC	93	0.31
NTS-24V-3.2A	85...264VAC 120...370VDC	24	3.2	76.8	40 / 230 VAC	55.5	0.6
NTS-24V-5A	88...132/176...264VAC 248...370VDC	24	5	120	40 / 230 VAC	65.5	0.79
NTS-24V-10A	85...264VAC 120...370VDC	24	10	240	45 / 230 VAC	125.5	1.2
NTS-24V-20A	90...132/180...264 VAC 254...370 VAC	24	20	480	40 / 230 VAC	227	2.6
NTS-24V-40A	340...550VAC 3ph.	24	40	960	50	276	3.3
NTS-48V-2.5A	88...132/176...264VAC 248...370VDC	48	2.5	120	40 / 230 VAC	65.5	0.79
NTS-48V-5A	85...264VAC 120...370VDC	48	5	240	45 / 230 VAC	125.5	1.2
NTS-48V-10A	180...264 VAC 250...370 VDC	48	10	480	40 / 230 VAC	227	2.6
NTS-48V-20A	340...550VAC 3ph.	48	20	960	50	276	3.3

尺寸图 (单位MM)

