



Major diameter	[mm]	5.0	0/-0.15
Minor diameter	[mm]	3.7	0/-0.462




Surface specification  
DIN ISO 1302

General tolerances  
DIN ISO 2768- mK

Work piece edge  
DIN ISO 13715

Scale: 2:1  
Material: 1.4404

				 <b>Nanotec</b> <sup>®</sup> PLUG & DRIVE		Name	Date	THREADED SPINDLE  ZST5-2-200-1
2	revise chart	21.06.17	A.S.		DRN	A.S.	02.04.2013	
1	revise drawing	08.06.17	A.S.		CHKD	G.S.	02.04.2013	
REV	DESCRIPTION	DATE	DRN					