


Major diameter	[mm]	6.0	0/-0.15
Minor diameter	[mm]	4.7	0/-0.462




Surface specification
DIN ISO 1302

General tolerances
DIN ISO 2768- mK

Work piece edge
DIN ISO 13715

Scale: 2:1
Material: 1.4404

REV	DESCRIPTION	DATE	DRN				Name	Date	THREADED SPINDLE ZST6-2-1500
2	revise chart	21.06.17	A.S.				DRN	J.D.	
1	revise drawing	08.06.17	A.S.	CHKD	G.S.	28.03.2014			