



Major diameter	[mm]	6.0	0/-0.15
Minor diameter	[mm]	4.7	0/-0.462

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: 2:1 Material: 1.4404	
4	revise chart	21.06.17	A.S.	 Nanotec PLUG & DRIVE			Name	Date	
3	revise drawing	08.06.17	A.S.				DRN	J.W.	11.02.2010
2	spindle material	06.06.12	J.W.				CHKD	S.Ha.	11.02.2010
1	tolerance add.	02.08.10	J.W.						
REV	DESCRIPTION	DATE	DRN						
								THREADED SPINDLE	
								ZST6-2-200-1	