





GPLK42-23 for DF45

GPLK42-23 for NEMA 17



use EJOT Delta PT screw  
WN5452 40x...  
Tmax. = 1.6 +0.2Nm



GEARBOX SPECIFICATION	
Reduction Ratio	22.66
No. of Stages	2
Rated Output Torque	Nm 6.0
Max. Output Torque	Nm 12.0
Max. Input Speed	rpm 5000
Backlash	° 1.5
Efficiency	% 70
Lifetime	h 5000
Max. Axial Force	N 40
Max. Radial Force (shaft middle)	N 40
Ambient Temperature	°C -15 ... 65



ISO 8015	ISO 1302	ISO 2768 cK	ISO 13715	Material:	Weight: ~0.18 kg	
			Date	Name	<b>GPLK42-23</b>	
			Drawn	18.10.2018		Schneid_A
			Reviewed	23.10.2018		Naubert_A
			Released	23.10.2018	Naubert_A	<b>12200030</b>
01	change max. amb. temp.	Schneid_A	09.11.2021	<b>Scale: 1 : 1</b> A4 Page 1		
REV	Rev. Text	Name	Date			<b>State: Released</b> Rev: 01    CONFIDENTIAL

