




				General tolerances ISO 2768-m		Work piece edges DIN 6784		Scale:			
								Material:			
								Surface:			
					Datum	Name					
				DRN	2025/10/14	L X					
				CHKD	2025/10/14	X T					
				APVD	2025/10/14	GYQ					
								CLC3-x-02			
								1			
								A3			
Rev	Description	Date	Name								