


DIMENSION (UNIT : mm)



PIN ASSIGNMENT		
PIN NO.	COLOR	FUNCTION
PIN 1	BK	0 V
PIN 2	RD	V _{cc}
PIN 3	GN	A
PIN 4	BN	A\
PIN 5	GY	B\
PIN 6	WH	B
PIN 7	YE	I\
PIN 8	OG	I

				 Nanotec [®] PLUG & DRIVE	APVD	M.S.	28.10.10	ENCODERCABLE-WEDL
2	change tolerances	14.09.16	A.S.		CHKD			
1	I AND I\ INTERCHANGED	18.05.11	J.W.	Surface specification DIN ISO 1302	DRN	J.W.	28.10.10	DWG.NO
REV	DESCRIPTION	DATE	DRN		General tolerances DIN ISO 2768- cH	SIGNATURE		DATE
				Work piece edge DIN ISO 13715				