


DIMENSION (UNIT : mm)



PIN ASSIGNMENT

| PIN NO. | COLOR | FUNCTION |
|---------|-------|-----------------|
| PIN 1 | BK | 0 V |
| PIN 2 | RD | V _{cc} |
| PIN 3 | GN | A |
| PIN 4 | BN | A\ |
| PIN 5 | GY | B\ |
| PIN 6 | WH | B |
| PIN 7 | YE | I\ |
| PIN 8 | OG | I |

| | | | | | | | | | | |
|--------|-----------------------|----------|------|---------------------------------------|--|----------------------------------|-----------|--------------------------|------------------|--------|
| 3 | change tolerance | 14.09.16 | A.S. | Nanotec PLUG & DRIVE | APVD | M.S. | 28.10.10 | ENCODERCABLE-WEDL | | |
| 2 (4x) | NEW TOLERANCE | 25.06.13 | A.S. | | CHKD | | | | | |
| 1 | I AND I\ INTERCHANGED | 18.05.11 | J.W. | Surface specification DIN ISO 1302 | General tolerances DIN ISO 2768- cH | Work piece edge DIN ISO 13715 | DRN | J.W. | 28.10.10 | DWG.NO |
| REV | DESCRIPTION | DATE | DRN | | | | SIGNATURE | DATE | ZK-WEDL-8-2000-S | |