


DIMENSION (UNIT : mm)



Pin Assignment Connector
JST-EHR-6

| Pin No. | Color | Function |
|---------|-------|-----------|
| 1 | GY | Shielding |
| 2 | BK | A |
| 3 | GN | A\ |
| 4 | RD | B |
| 5 | BU | B\ |
| 6 | GY | Shielding |

Twisted
Twisted

| | | | | | | | | | |
|--------|------------------|--------|------|---|------------|-----------|-------|----------|------------------------|
| | | | | Nanotec [®] PLUG & DRIVE | SCALE FREE | APVD | G.S. | 02.01.13 | EXTENSION CABLE |
| A (7x) | CHANGE TOLERANCE | 7.5.13 | A.S. | | X ±0.5 | CHKD | | | |
| REV | DESCRIPTION | DATE | APVD | ZK-JST-EHR-6-0,5M-S | 1PL ±0.2 | DRN | A.S.. | 02.01.13 | ZK-JST-EHR-6-0,5M-S |
| | | | | | 2PL ±0.1 | SIGNATURE | DATE | | |
| | | | | | ANGLE ±30' | | | | |