


10	CONNECTOR	
JST VHR-2N / Contact: SVH-41T-P1.1		
Contact Resistance	mΩ	≤10
Contact Material	Phosphor bronze, Tin plated	
Contact Carrier Material	n. a.	
Connector Body Material	PA66, natural (white), UL94V-0	
Protection Class	n. a.	
	Pin No.	Colour
	1	RD
	2	BK

20	CABLE SPECIFICATION		
Cable Length	mm	500	
Cable Diameter	mm	n.a.	
Cable Material	n.a.		
Cable Color	n.a.		
Conductor Insulation	n.a.		
Conductor / Cross - Section	2xAWG16		
UL Type	UL1332		
Shielded	No		
Bending Radius (flexible)	n.a.		
Bending Radius (stationary)	n.a.		

ISO 8015	ISO 1302	ISO 2768 cK	ISO 13715	Weight: ~0.05 kg
			Date	ZK-VHR-2-500
			Name	
			Drawn 16.03.2021 Schneid_A	
			Reviewed 17.03.2021 Reith_S	
			Released 17.03.2021 Reith_S	20000911
REV	Rev. Text	Name	Date	
			State: Released	
			Rev: 00	CONFIDENTIAL