



10	<b>CONNECTOR</b>	
JST VHR-3N / Contact: SVH-41T-P1.1		
Contact Resistance	mΩ	≤10
Contact Material	Phosphor bronze, Tin plated	
Contact Carrier Material	n. a.	
Connector Body Material	PA66, natural (white), UL94V-0	
Protection Class	n. a.	
	<b>Pin No.</b>	<b>Colour</b>
	1	RD
	2	GN
	3	BK

20	<b>CABLE SPECIFICATION</b>		
Cable Length	mm	500	
Cable Diameter	mm	n.a.	
Cable Material	n.a.		
Cable Color	n.a.		
Conductor Insulation	n.a.		
Conductor / Cross - Section	3xAWG16		
UL Type	UL1332		
Shielded	No		
Bending Radius (flexible)	n.a.		
Bending Radius (stationary)	n.a.		

ISO 8015	ISO 1302	ISO 2768 cK	ISO 13715	Weight: ~0.05 kg
				 <b>ZK-VHR-3-500</b>
			Date: 17.03.2021 Name: Schneid_A	
			Drawn: 17.03.2021 Reviewed: 17.03.2021 Released: 17.03.2021 Name: Reith_S	
01	new revised drawing			
REV	Rev. Text	Name	Date	 <b>20000913</b> State: Released    Rev: 01    CONFIDENTIAL