



10 CABLE SPECIFICATION		
Cable Length	mm	2000
Cable Diameter	mm	9.3
Cable Material		PUR
Cable Color		Black
Conductor Insulation		PP
Conductor / Cross - Section		4x AWG14
UL Type		UL 20549
Shielded		Yes
Bending Radius (flexible)		Min. 15 x Ø
Bending Radius (stationary)		Min. 12 x Ø
GENERAL SPECIFICATION		
Rated Current	A	16
Rated Voltage	VAC/DC	-/63
Insulation resistance	MΩ	≥100
Ambient temperature		-10°C...+80°C

20 CONNECTOR		
M12 / 4-Pole / L-Coding / female / straight		
Contact Resistance	mΩ	≤5
Contact Material	Brass, Gold-Plated	
Contact Carrier Material	PA	
Connector Body Material	TPU	
Coupling (Nut / Screw)	Brass, Nickel-Plated	
O-Ring Material	FKM	
Protection Class	IP67 (locked Condition)	
Pin No.	Color	
1	RD	
2	RD/WH	
3	BK	
4	BK/WH	
Coupling	Braid	

ISO 8015	ISO 1302	ISO 2768 cK	ISO 13715	Weight: -	kg
			Date	Name	
			Drawn	28.07.2020	Schneid_A
			Reviewed	06.08.2020	Reith_S
			Released	06.08.2020	Reith_S
REV	Rev. Text	Name			
				20000563	A4 Page 1
				State: Released	Rev: 00 CONFIDENTIAL