



10		CONNECTOR A	
M12 / 5-Pole / B-Coding / female / angled			
Contact Resistance	mΩ	≤5	
Contact Material	Brass, Gold-Plated		
Contact Carrier Material	PA		
Connector Body Material	TPU		
Coupling ( Nut / Screw)	Brass, Nickel-Plated		
O-Ring Material	FKM		
Protection Class	IP67 (locked Condition)		
<b>Pin No.</b>		<b>Color</b>	
1		BN	
2		WH	
3		BU	
4		BK	
5		GY	
Coupling		Braid	

20 CABLE SPECIFICATION		
Cable Length	mm	2000
Cable Diameter	mm	5.5
Cable Material	PUR	
Cable Color	Black	
Conductor Insulation	PVC	
Conductor / Cross - Section	5x AWG22	
UL Type	UL 20549	
Shielded	Yes	
Bending Radius (flexible)	Min. 15 x Ø	
Bending Radius (stationary)	Min. 12 x Ø	

GENERAL SPECIFICATION		
Rated Current	A	4
Rated Voltage	VAC/DC	60
Insulation resistance	MΩ	≥100
Ambient temperature	-10°C...+80°C	

ISO 8015		ISO 1302		ISO 2768-1 cK		ISO 13715		Weight: 0.12 kg	
				Drawn	12.12.2017	Name		ZK-M12-5-2M-2-B-S	
				Checked	12.12.2017	Schneid_A			
				Approved	12.12.2017	Knoll_J			
01	revise drawing	Schneid_A	16.10.2018			14200001		-	
REV	Rev. Text	Name	Rel. Date			State: Released		Rev: 01	P