



10	<b>CONNECTOR A</b>		
MOLEX: 2074580003 / Contact AWG18: 455703050 alternativ 455703000			
Contact Resistance	mΩ	≤10	
Contact Material	Tin over Copper Alloy		
Contact Carrier Material	n. a.		
Connector Body Material	Nylon 6/6		
Protection Class	94V-2		
PIN No.	Colour	Function	Lead Gauge
1	RD	V	AWG 18
2	BK	W	AWG 18
3	YE	U	AWG 18

20	<b>CABLE SPECIFICATION</b>	
Cable Length	mm	500
Conductor Insulation	UL1332: Teflon	
UL Type	UL1332 AWG18	
Conductor / Cross - Section	3xAWG18	

<b>GENERAL SPECIFICATION</b>		
Rated Current	A	n. a.
Rated Voltage	VAC/DC	n. a.
Insulation resistance	MΩ	n. a.
Ambient temperature	n. a.	

ISO 8015	ISO 1302	ISO 2768 cK	ISO 13715	Weight: ~0.03 kg
			Date	Name
			Drawn	21.01.2021 Schneid_A
			Reviewed	21.01.2021 Hofstet._M
			Released	21.01.2021 Hofstet._M
REV	Rev. Text	Name	Date	



<b>ZK-DF90-E-500</b>	
20000780	A4 Page 1
State: Released	Rev: 00 CONFIDENTIAL