

DATASHEET

USB-A to USB-C cable 60W QC 3A 2m grey gold contacts textile coat



General data

USB-A to USB Type-C Charging Cable - 60W Power, Textile Braid, 0.5-3m

High-performance **USB-A to USB Type-C cable** designed for industrial, IT, and retail environments. Built for **up to 60W charging power**, durability, and eco-conscious packaging – ideal for resellers, integrators, and business customers.

Product Features:

- **USB-A to USB Type-C cable**, compliant with **USB 2.0 standard**
- **Supports up to 60W** and the Quick Charging Standard **QC**
- **480 Mbps** data transfer speed
- **Available lengths:** 0.5 m / 1 m / 2 m / 3 m
- **Gold-plated USB-A and USB Type-C connectors** with **aluminum housing**

This datasheet was created automatically on 24-03-2026 . Technical changes reserved.

DATASHEET

USB-A to USB-C cable 60W QC 3A 2m grey gold contacts textile coat

- **Durable textile-braided jacket in space-grey** – flexible and wear-resistant
- **Printed charging bolt symbol** on the connector for function identification (not an LED)
- **Plastic-free individual packaging** – shipping-ready without overpack
- **No plastic accessories:** paper twist-tie with metal wire, no dust caps
- **Use Cases:**

Ideal for workplace infrastructure, mobile device accessories, corporate IT rollouts, public charging points, and OEM bundling. Compatible with USB-C laptops, smartphones, tablets, and more.

Technical properties	
3D	False
ARC	False
Backwards compatible	True
Bending radius (dynamic/static)	40 mm
CEC	False
Cable set	False
Cable type (passive/active/optical)	passive
Chip	False
Connection type connection 1	Plug
Connection type connection 2	Plug
Connector 1 angulation	180°
Connector 2 angulation	180°
Contact Plating	gold-plated
DSC	False
Dust cover	false
Fast Charging technologie	QC 2.0
HDMI Power	False
HDMI certified	False
HEC (Ethernet channel)	False
Halogenfree	No
Kink protection	True
MSA	False
MST	False
Material Connector Housing	Aluminium
Material Inner Conductor	BC

This datasheet was created automatically on 24-03-2026 . Technical changes reserved.

DATASHEET

USB-A to USB-C cable 60W QC 3A 2m grey gold contacts textile coat

Material jacket	PVC+Textile
Max. mating cycles	10000
Model	Round Cable
Number of poles connection 1	4
Number of poles connection 2	4
Number of shieldings	double
Operating temperature	-5 - 45 °C
PCIe Data transfer	False
Plug dimensions Side 1	12 x 4.5 x 20.5mm
Plug dimensions Side 2	8.25 x 2.35 x 14.5mm
Power Delivery	60 W
Scope of delivery	1xUSB Cable
Shielded	True
Speed	480 Mbit/s
Storage Temperature	-20 - 70 °C
Tensile strength (short/long)	98,1 N
Type of connector connection 1	USB-A
Type of connector connection 2	USB Type-C
Type of packaging	paper box
VESA certified	False
VRR	False
Version	USB 2.0 High-Speed
Warranty	36 months
With termination resistor	False
eARC	False

Available variants

ArtNr.	Bezeichnung	Color	Length	Diameter	AWG
USB-AC-00001	USB-A to USB-C cable 60W QC 3A 0.5m grey gold contacts textile coat	space grey	0.5 m	4.0 mm	22AWG
USB-AC-00002	USB-A to USB-C cable 60W QC 3A 1m grey gold contacts textile coat	space grey	1 m	4.0 mm	22AWG
USB-AC-00003	USB-A to USB-C cable 60W QC 3A 2m grey gold contacts textile coat	space grey	2 m	4.0 mm	22AWG
USB-AC-00004	USB-A to USB-C cable 60W QC 3A 3m grey gold contacts textile coat	space grey	3 m	4.0 mm	22AWG

This datasheet was created automatically on 24-03-2026 . Technical changes reserved.

