



A →



Thread code:UGFC	
Thread type	ACME
Major diameter(mm)	5.017...5.331
Minor diameter(mm)	3.493...3.620
Lead	5.08
Pitch	1.27
Starts	4

General tolerances ISO 2768-m		Work piece edges DIN 6784		Scale:	
Datum		Name		Material: POM	
DRN	2018/4/26	L	W	Surface:	
CHKD	2018/4/26	X	T	External linear nut	
APVD	2018/4/26	P.R.			
					
				LSNUT-AAAA-UGFC	
				1	
				A3	
1	-	18.04.19	X	T	
Rev	Description	Date	Name		