


Thread code: UIAP	
Thread type	ACME
Major diameter(mm)	5.812...6.066
Minor diameter(mm)	4.948...5.075
Lead	0.6096
Pitch	0.6096
Starts	1

General tolerances ISO 2768-m				Work piece edges DIN 6784		Scale:	
			Datum	Name	Material: POM		
			DRN	2018/4/13	X	T	External linear nut
			CHKD	2018/4/13	GYQ		
			APVD	2018/4/13	P.R.		
					Surface:		
1	-	18.04.19	X	T	 LSNUT-AAAE-UIAP		
A	-	27.04.18	X	T			
Rev	Description	Date	Name				A3