



Thread code: UIEV	
Thread type	ACME
Major diameter(mm)	5.812...6.167
Minor diameter(mm)	4.338...4.501
Lead	4.8768
Pitch	1.2192
Starts	4

				General tolerances ISO 2768-m	Work piece edges DIN 6784	Scale:	
				Datum	Name	Material: POM	
				DRN	2018/7/27	Surface:	
				CHKD	2018/7/27	External linear nut	
				APVD	2018/7/27	LSNUT-AAAAE-UIEV	
							1
							A3
A	-	12.04.19	X T				
Rev	Description	Date	Name				