



Thread code:TJBA	
Thread type	Trapezoid
Major diameter(mm)	6.300min
Minor diameter(mm)	5.000...5.150
Lead	1
Pitch	1
Starts	1

Spring data	
Test length L1(mm)[in]	8.92[0.35]
Force at L1(N)[lb]	20.91[4.7]
Spring rate(N/mm)[lb/in]	3.061[17.479]

General tolerances ISO 2768-m		Work piece edges DIN 6784		Scale:3:1	
Material: POM		Surface:		axial-compensated nut	
Date		Name		LSNUT-AEAE-TJBA	
DRN 2018/4/16		L W		1	
CHKD 2018/4/16		X T		A3	
APVD 2018/4/16		P.R.			
Rev		Description		Date	

