



Thread code:TJCA	
Thread type	Trapezoid
Major diameter(mm)	6.300min
Minor diameter(mm)	5.000...5.150
Lead	2
Pitch	1
Starts	2

Spring data	
Test length L1(mm)[in]	8.92[0.35]
Force at L1(N)[lb]	20.91[4.7]
Spring rate(N/mm)[lb/in]	3.061[17.479]

General tolerances ISO 2768-m		Work piece edges DIN 6784		Scale:3:1	
Material: POM		Surface:		axial-compensated nut	
Datum		Name			
DRN	2018/4/16	L	W		
CHKD	2018/4/16	X	T		
APVD	2018/4/16	P.	R.	LSNUT-AEAE-TJCA	
Rev	Description	Date	Name	A3	