



Thread code:UIEV	
Thread type	ACME
Major diameter(mm)	5.812...6.167
Minor diameter(mm)	4.338...4.501
Lead	4.8768
Pitch	1.2192
Starts	4
Thread per inch	20.83

Spring data	
Test length L1(mm)[in]	8.92[0.35]
Force at L1(N)[lb]	20.91[4.7]
Spring rate(N/mm)[lb/in]	3.061[17.479]

General tolerances ISO 2768-m		Work piece edges DIN 6784		Scale:3:1	
Datum		Name		Material: POM	
DRN	2018/7/27	L	W	Surface:	
CHKD	2018/7/27	X	T	axial-compensated nut	
APVD	2018/7/27	P	R.		
				LSNUT-AEAE-UIEV	
				1	
Rev				A3	
Description		Date		Name	