



Thread code:UKAS	
Thread type	ACME
Major diameter(mm)	6.604...6.858
Minor diameter(mm)	5.555...5.682
Lead	0.79375
Pitch	0.79375
Starts	1

Spring data	
Test length L1(mm)[in]	8.92[0.35]
Force at L1(N)[lb]	20.91[4.7]
Spring rate(N/mm)[lb/in]	3.061[17.479]

General tolerances ISO 2768-m		Work piece edges DIN 6784		Scale:3:1	
Datum		Name		Material: POM	
DRN 2018/4/17		L W		Surface:	
CHKD 2018/4/17		X T		axial-compensated nut	
APVD 2018/4/17		P.R.			
				LSNUT-AEAE-UKAS	
Rev				Description	
Date				Name	
				1	
				A3	