



Thread code:THCA	
Thread type	Trapezoidal
Major diameter(mm)	5.300 min
Minor diameter(mm)	4.000...4.150
Lead	2
Pitch	1
Starts	2

Spring data	
Test length L1(mm)[in]	8.92 [0.35]
Force at L1(N)[lb]	20.91 [4.7]
Spring rate(N/mm)[lb/in]	3.061 [17.479]

General tolerances ISO 2768-m		Work piece edges DIN 6784		Scale: 3:1	
Datum		Name		Material: POM	
DRN	2021/8/4	X	T	Surface:	
CHKD	2021/8/4		GYQ	axial-compensated nut	
APVD					
				LSNUT-AEAE-THCA	
				1	
Rev				A3	
Description		Date		Name	