



Thread code:UGFC	
Thread type	ACME
Major diameter(mm)	5.017...5.331
Minor diameter(mm)	3.493...3.620
Lead	5.08
Pitch	1.27
Starts	4

Spring data	
Test length L1(mm)[in]	8.92 [0.35]
Force at L1(N)[lb]	20.91 [4.7]
Spring rate(N/mm)[lb/in]	3.061 [17.479]

General tolerances ISO 2768-m		Work piece edges DIN 6784	Scale: 3:1	
Datum		Name	axial-compensated nut	
DRN	2021/8/4	X T		
CHKD	2021/8/4	GYQ		
APVD				
		Nanotec PLUG & DRIVE	LSNUT-AEAE-UGFC	
Rev	Description	Date	Name	1 A3