



Thread code:TSGA	
Thread type	Trapezoidal
Major diameter(mm)	10.500 Min
Minor diameter(mm)	7.000...7.315
Lead	6
Pitch	3
Starts	2

Spring data	
Test length L1(mm)[in]	12.01[0.47]
Force at L1(N)[lb]	36.13[8.12]
Spring rate(N/mm)[lb/in]	2.699[15.41]

General tolerances ISO 2768-m		Work piece edges DIN 6784		Scale: 3:1	
Datum		Name		Material: POM	
DRN	2021/11/5	X	T	Surface:	
CHKD	2021/11/5	GYQ		axial-compensated nut	
APVD	2021/11/5	P.R.			
				LSNUT-AEAJ-TSGA	
				1	
Rev				A3	
Description				Date	
Name					