



Thread code:TSCA	
Thread type	Trapezoidal
Major diameter(mm)	10.500 Min
Minor diameter(mm)	8.000...8.236
Lead	2
Pitch	2
Starts	1

Spring data	
Test length L1(mm)[in]	12.01[0.47]
Force at L1(N)[lb]	36.13[8.12]
Spring rate(N/mm)[lb/in]	2.699[15.41]

General tolerances ISO 2768-m				Work piece edges DIN 6784		Scale: 3:1	
Datum				Name		Material: POM	
DRN 2021/8/11				X T		Surface:	
CHKD 2021/8/11				GYQ		axial-compensated nut	
APVD 2021/8/11				P.R.			
Nanotec <small>PLUG & DRIVE</small>						LSNUT-AFAJ-TSCA	
						1	
Rev		Description		Date		Name	
						A3	