



Thread code:UQBN	
Thread type	ACME
Major diameter(mm)	9.779...10.033
Minor diameter(mm)	7.938...8.065
Lead	1.5875
Pitch	1.5875
Starts	1

Spring data	
Test length L1(mm)[in]	12.01[0.47]
Force at L1(N)[lb]	36.13[8.12]
Spring rate(N/mm)[lb/in]	2.699[15.41]

General tolerances ISO 2768-m				Work piece edges DIN 6784		Scale: 3:1	
Datum				Name		Material: POM	
DRN				2021/8/11		X T	
CHKD				2021/8/11		GYQ	
APVD				2021/8/11		P.R.	
						axial-compensated nut	
						LSNUT-AFAJ-UQBN	
Rev						A3	
Description				Date		Name	