



Thread code:TJBA	
Thread type	Trapezoid
Major diameter(mm)	6.300min
Minor diameter(mm)	5.000...5.150
Lead	1
Pitch	1
Starts	1

Spring data	
Test length L1(mm)[in]	8.92[0.35]
Force at L1(N)[lb]	20.91[4.7]
Spring rate(N/mm)[lb/in]	3.061[17.479]

General tolerances ISO 2768-m				Work piece edges DIN 6784		Scale:	
Material: TECAFORM AD AF				Surface:			
Datum		Name		axial-compensated nut			
DRN	2021/3/3	X	T				
CHKD	2021/3/3	GYQ					
APVD	2021/3/3	P.R.					
				LSNUT-AFAE-TJBA		1	
						A3	
Rev	Description	Date	Name				