



| Thread code:TJBA | |
|--------------------|---------------|
| Thread type | Trapezoid |
| Major diameter(mm) | 6.300min |
| Minor diameter(mm) | 5.000...5.150 |
| Lead | 1 |
| Pitch | 1 |
| Starts | 1 |

| | | | | General tolerances ISO 2768-m | Work piece edges DIN 6784 | Scale: | |
|-----|-------------|----------|------|----------------------------------|------------------------------|------------------------|----|
| | | | | Datum | Name | Material: POM | |
| | | | | DRN | 2020/9/11 | P.R. | |
| | | | | CHKD | 2020/9/11 | X T | |
| | | | | APVD | 2020/9/11 | GYQ | |
| | | | | | | LSNUT-AGAE-TJBA | 1 |
| | | | | | | | A3 |
| A | - | 11.11.20 | X T | | | | |
| Rev | Description | Date | Name | | | | |