



Thread code:TJCA	
Thread type	Trapezoid
Major diameter(mm)	5.888...6.000
Pitch diameter(mm)	5.283...5.440
Minor diameter(mm)	4.444...4.700
Lead	2
Pitch	1
Starts	2
Thread per inch	25.4

Spring data	
Test length L1(mm)[in]	8.92[0.35]
Force at L1(N)[lb]	20.91[4.7]
Spring rate(N/mm)[lb/in]	3.061[17.479]

General tolerances ISO 2768-m				Work piece edges DIN 6784		Scale:	
						Material: POM	
						Surface:	
Datum		Name		axial-compensated nut			
DRN 2018/5/30		L W					
CHKD 2018/5/30		GYQ					
APVD							
				Nanotec [®] PLUG & DRIVE		LSNUT-AFAE-TJCA	
Rev		Description		Date		Name	
						1	
						A3	