



Thread code: TSGA	
Thread type	Trapezoidal
Major diameter(mm)	10.500 Min
Minor diameter(mm)	7.000...7.315
Lead	6
Pitch	3
Starts	2

General tolerances ISO 2768-m				Work piece edges DIN 6784		Scale:		
						Material: POM		
						Surface:		
				Datum	Name	External linear nut		
				DRN	2018/9/3			X T
				CHKD	2018/9/3			GYQ
				APVD	2018/9/3			P.R.
				<b>Nanotec</b> PLUG & DRIVE		LSNUT-AAAG-TSGA		
						1		
A	-	12.04.19	X T			A3		
Rev	Description	Date	Name					