



| Thread code:UIEV   |               |
|--------------------|---------------|
| Thread type        | ACME          |
| Major diameter(mm) | 5.812...6.167 |
| Minor diameter(mm) | 4.338...4.501 |
| Lead               | 4.8768        |
| Pitch              | 1.2192        |
| Starts             | 4             |

|     |             |          |      |                                  |                              |                       |                 |
|-----|-------------|----------|------|----------------------------------|------------------------------|-----------------------|-----------------|
|     |             |          |      | General tolerances<br>ISO 2768-m | Work piece edges<br>DIN 6784 | Scale:                |                 |
|     |             |          |      | Datum                            | Name                         | Material: POM         |                 |
|     |             |          |      | DRN                              | 2020/9/11                    | Surface:              |                 |
|     |             |          |      | CHKD                             | 2020/9/11                    | Axial-compensated nut |                 |
|     |             |          |      | APVD                             | 2020/9/11                    |                       |                 |
|     |             |          |      |                                  |                              |                       | LSNUT-AGAE-UIEV |
|     |             |          |      |                                  |                              |                       |                 |
| A   | -           | 11.11.20 | X T  |                                  |                              |                       | 1               |
| Rev | Description | Date     | Name |                                  |                              |                       | A3              |