



| Thread code:UKAS | |
|--------------------|---------------|
| Thread type | ACME |
| Major diameter(mm) | 6.604...6.858 |
| Minor diameter(mm) | 5.555...5.682 |
| Lead | 0.79375 |
| Pitch | 0.79375 |
| Starts | 1 |

| | | | | | | | |
|-----|-------------|----------|------|----------------------------------|------------------------------|-----------------------|--|
| | | | | General tolerances ISO 2768-m | Work piece edges DIN 6784 | Scale: | |
| | | | | Datum | Name | Material: POM | |
| | | | | DRN | 2020/9/11 | Surface: | |
| | | | | CHKD | 2020/9/11 | Axial-compensated nut | |
| | | | | APVD | 2020/9/11 | | |
| | | | | | | LSNUT-AGAE-UKAS | |
| | | | | | | | |
| A | - | 11.11.20 | X T | | | 1 | |
| Rev | Description | Date | Name | | | A3 | |