



Thread code:UKGI	
Thread type	ACME
Major diameter(mm)	6.604...6.960
Minor diameter(mm)	4.763...4.943
Lead	6.350
Pitch	1.5875
Starts	4

Spring data	
Test length L1(mm)[in]	8.92[0.35]
Force at L1(N)[lb]	20.91[4.7]
Spring rate(N/mm)[lb/in]	3.061[17.479]

General tolerances ISO 2768-m		Work piece edges DIN 6784		Scale:			
Material: TECAFORM AD AF		Surface:		axial-compensated nut			
DRN	2021/3/3	X	T				
CHKD	2021/3/3	GY	Q				
APVD	2021/3/3	P.	R.				
Rev		Description		Date		Name	
1		LSNUT-AFAE-UKGI				1	
						A3	

